



TECHNICAL INFORMATION

Watts:	24
Lumens:	3000
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	White
Body Type:	Nano Plastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	160°
Color Temperature:	4000K
Dimension:	1500x28mm
lumens per watt:	125

T8 PRO TUBES | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21674 - 24 White

[View more details](#)

G13 NANOPLASTIC LED TUBE



5
FEET

5 YEAR
WARRANTY

Better light transmittance and angle - diffuses glare
No Flickering | No UV radiation | No Mercury



FEATURES

- Nano-plastic tube offers better light transmittance - Lumen efficiency of 125 LM/W
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Fitted with high efficiency SMD-Samsung Chip LED Chips
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more



PACKAGING

Gross Weight (Kgs): 0.19
Unit CBM: 0.001766
Dimension: 1500x28mm

MASTER BOX PACKAGING

Box Qty: 25
Length (Box) mm: 1548
Width (Box) mm: 29
Height (Box) mm: 29

LISTING DETAILS

Commodity Code: 85395200
Ean Code: 3800157664813