



TECHNICAL INFORMATION

Watts:	6.5
Lumens:	600
Shape:	G45
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	180°
Color Temperature:	6500K
Equivalence Watts:	45
Dimension:	45x89mm



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 45 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

GOLF E27 PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21868 - 6.5 White

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.03
Unit CBM: 0.00025
Dimension: 45x89mm

MASTER BOX PACKAGING

Box Qty: 10
Length (Box) mm: 45
Width (Box) mm: 45
Height (Box) mm: 80

LISTING DETAILS

Commodity Code: 85395200
Ean Code: 3800157677479