



TECHNICAL INFORMATION

Watts:	4.5
Lumens:	470
Shape:	G45
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	180°
Color Temperature:	3000K
Equivalence Watts:	40
Dimension:	45x80mm



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for B22 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

GOLF B22 PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21104 - 4.5 White

[View more details](#)



PACKAGING

Gross Weight (Kgs):	0.04
Unit CBM:	0.00031
Dimension:	45x80mm

MASTER BOX PACKAGING

Box Qty:	12
Length (Box) mm:	50
Width (Box) mm:	5
Height (Box) mm:	110

LISTING DETAILS

Commodity Code:	9405403990
Ean Code:	3800157676496