



TECHNICAL INFORMATION

Watts:	8.5
Lumens:	806
Shape:	A60
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	200°
Color Temperature:	3000K
Equivalence Watts:	60
Dimension:	60x108mm



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 60 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for B22 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

GLS B22 PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21101 - 8.5 White

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.05
Unit CBM: 0.000625
Dimension: 60x108mm

MASTER BOX PACKAGING

Box Qty: 12
Length (Box) mm: 59
Width (Box) mm: 59
Height (Box) mm: 106

LISTING DETAILS

Commodity Code: 9405403990
Ean Code: 3800157675086