



TECHNICAL INFORMATION

Watts:	3
Lumens:	330
Input Power:	AC:220-240V,50Hz
Long Life:	20,000 Hours
Unit Color:	Transparent
Body Type:	Plastic
PF:	>0.4
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	300°
Color Temperature:	3000K
Equivalence Watts:	30
Dimension:	49x17mm



FEATURES

- Stable SMD-Samsung Chip technology for better reliability
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces watts old halogen lamp
- Easy to install, designed with G9 base
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

G9 CAPSULES PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21246 - 3 Transparent

[View more details](#)



PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000211
Dimension:	49x17mm

MASTER BOX PACKAGING

Box Qty:	400
Length (Box) mm:	30
Width (Box) mm:	70
Height (Box) mm:	110

LISTING DETAILS

Commodity Code:	85395200
Ean Code:	3800157677721