

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510210400](#)
Status: **Active**
Overview: [PicoBlade Connector System](#)
Description: 1.25mm Pitch, PicoBlade Receptacle Crimp Housing, Single Row, Friction Lock, 4 Circuits, Natural



Documents:

Drawing (PDF)	Product Specification 510211109-PS-000 (PDF)
2D Drawing (DXF)	Product Specification 510211110-PS-000 (PDF)
3D Model	Product Specification 510211111-PS-000 (PDF)
2D Drawing DXF (PDF)	Product Specification 510211124-PS-000 (PDF)
3D Model (PDF)	Product Specification PS-51021-009-001 (PDF)
Product Specification 510210000-PS-000 (PDF)	Product Specification PS-51021-024-001 (PDF)
Product Specification 510210001-PS-000 (PDF)	Product Specification PS-51021-025-001 (PDF)
Product Specification 510210006-PS-000 (PDF)	Application Specification 510210000-AS-000 (PDF)
Product Specification 510211000-PS-000 (PDF)	Application Specification 510210001-AS-000 (PDF)
Product Specification 510211001-PS-000 (PDF)	Packaging Specification SPK-51021-001-001 (PDF)
Product Specification 510211009-PS-000 (PDF)	Datasheet (PDF)
Product Specification 510211010-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 510211024-PS-000 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51021
Application	Signal, Wire-to-Board, Wire-to-Wire
Overview	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753575615

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	42.200/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	510210000-AS-000, 510210001-AS-000
Packaging Specification	SPK-51021-001-001
Product Specification	510210000-PS-000, 510210001-PS-000, 510210006-PS-000, 510211000-PS-000, 510211001-

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[51021 Series](#)

Mates With

PicoBlade Header [53261](#) , [53047](#) , [53398](#) ,
[53048](#) . PicoBlade Plug Housing [51047](#)

Use With

PicoBlade Crimp Terminal [50058](#) , [50079](#)
. PicoBlade Pre-Crimped Lead [214920](#)
, [214921](#) , [797580006](#) , [797580014](#) ,
[797581059](#) , [797581060](#) , [797581061](#) ,
[797581062](#) , [797581063](#)

Sales Drawing

PS-000, 510211009-PS-000, 510211010-
PS-000, 510211024-PS-000, 510211109-PS-000,
510211110-PS-000, 510211111-PS-000, 510211124-
PS-000, PS-51021-009-001, PS-51021-024-001,
PS-51021-025-001
510210000-SD-000, SD-51021-002-001

This document was generated on 07/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION