



TECHNICAL INFORMATION

Watts:	12
Lumens:	920
Input Power:	AC:100-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.6
LED Chip Type:	COB
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	20°
Color Temperature:	3000K
Dimension:	73x255mm



FEATURES

- Perfectly designed IP65 rated garden spike with LED
- Works perfectly in extreme temperatures (-20Â° to +45Â°)
- Strong and sturdy Aluminium body
- Suitable for pathways, stairways, corridors, walkways etc.



GARDEN SPIKES LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 217547 - 12 Black

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.45
Unit CBM: 0.00132
Dimension: 73x255mm

MASTER BOX PACKAGING

Box Qty: 50
Length (Box) mm: 90
Width (Box) mm: 85
Height (Box) mm: 155

LISTING DETAILS

Commodity Code: 94054239
Ean Code: 3800157681018