



## TECHNICAL INFORMATION

Watts:	5
Lumens:	645
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	Grey
Body Type:	Aluminium
PF:	>0.5
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	120°
Color Temperature:	4000K
Dimension:	170x170x75mm



## FEATURES

- Splendid designs made of high endurance Aluminium material
- Ingress protection: (ip\_rating)
- Excellent heat dissipation
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Perfect lighting option for landscapes, gardens, patios etc.

## MODERN WALL LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 218285 - 5 Grey

[View more details](#)



## PACKAGING

Gross Weight (Kgs):	0.73
Unit CBM:	0.00396
Dimension:	170x170x75mm

## MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	190
Width (Box) mm:	190
Height (Box) mm:	100

## LISTING DETAILS

Commodity Code:	94054239
Ean Code:	3800157678438