



## TECHNICAL INFORMATION

Watts:	5
Lumens:	700
Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.4
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-25°C to +50°C
Beam Angle:	120°
Color Temperature:	3000K
Dimension:	140x115x100mm



## FEATURES

- Modern range of Up-Down lights with sleek and stylish designs
- Elegant replacement for traditional up-down lighting
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Robust Aluminium build for efficient heat dissipation
- Suitable for living rooms, pathways, balconies, facades etc.

## ROUND BRIDGELUX | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 217081 - 5 Black

[View more details](#)



## PACKAGING

Gross Weight (Kgs):	0.72
Unit CBM:	0.00238
Dimension:	140x115x100mm

## MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	150
Width (Box) mm:	120
Height (Box) mm:	110

## LISTING DETAILS

Commodity Code:	94054239
Ean Code:	3800157678308