



TECHNICAL INFORMATION

Watts:	11
Lumens:	1360
Shape:	Square
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.4
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-25°C to +50°C
Beam Angle:	120°
Color Temperature:	3000K
Dimension:	100x100x100mm



FEATURES

- Modern range of Up-Down lights with sleek and stylish designs
- Elegant replacement for traditional up-down lighting
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Robust Aluminium build for efficient heat dissipation
- Suitable for living rooms, pathways, balconies, facades etc.

SQUARE BRIDGELUX | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218529 - 11 Black

[View more details](#)



SMD LED'S

Uses premium quality LEDs for a reliable, long-lasting, and energy saving light

PACKAGING

Gross Weight (Kgs):	0.71
Unit CBM:	0.001575
Dimension:	100x100x100mm

MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	110
Width (Box) mm:	110
Height (Box) mm:	110

LISTING DETAILS

Commodity Code:	94054239
Ean Code:	3800157678285