



PRISMATIC 120 LUMEN | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand. endless solutions..

SKU: 20349 - 20 White

[View more details](#)

TECHNICAL INFORMATION

Watts:	20
Lumens:	2400
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	White
Body Type:	Plastic
PF:	>0.7
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Dimmable:	No
Beam Angle:	120°
Color Temperature:	6500K
Dimension:	600x75x24mm
lumens per watt:	120



FEATURES

- Prismatic Fitting designed with Lumen efficiency 120LM/W
- Fitted with high efficiency SMD-Samsung Chip that offer up to 85% in energy savings
- Ballast or Starter not required, direct AC Power
- Long life span, low maintenance and energy saving
- No flickering, No UV radiation
- Applications - Residential, Hotels, Malls, Office and many more



PACKAGING

Gross Weight (Kgs): 0.25
Unit CBM: 0.001563
Dimension: 600x75x24mm

MASTER BOX PACKAGING

Box Qty: 30
Length (Box) mm: 625
Width (Box) mm: 78
Height (Box) mm: 26

LISTING DETAILS

Commodity Code: 9405114090
Ean Code: 3800157663717