



TECHNICAL INFORMATION

Watts:	6
Lumens:	445
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Plastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	Yes
Beam Angle:	38°
Color Temperature:	3000K
Equivalence Watts:	60
Dimension:	50x55mm



FEATURES

- Stable SMD-Samsung Chip technology for better reliability
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces watts old halogen lamp
- Easy to install, designed with GU10 base
- Built with dimming feature
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

GU10 LENS 38° DIMMABLE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21195 - 6 White

[View more details](#)

LED SPOTLIGHT



Equipped with LEDs provided by Samsung for maximum efficiency.

PACKAGING

Gross Weight (Kgs): 0.04
Unit CBM: 0.00025
Dimension: 50x55mm

MASTER BOX PACKAGING

Box Qty: 10
Length (Box) mm: 50
Width (Box) mm: 50
Height (Box) mm: 90

LISTING DETAILS

Commodity Code: 9405403990
Ean Code: 3800157676434