



## M211 Portable Bluetooth Label Printer

Part Number: M211

### Overview

Design. Preview. Print. All from your phone. The tough, compact labeler that belongs on any jobsite.

- Seamlessly design, preview and print labels right from our industry-leading Express Labels Mobile app for iOS and Android

- Create custom labels from your phone's familiar keyboard via ultra strong BLE Bluetooth technology
- Maximize on-site efficiency — import data, save and share files with ease. Plus, get more done with 22 barcode/QR code types, 85 fonts and over 14,000 symbols
- Work all day and print over 300 labels on a single charge using advanced Li-Ion battery technology
- Get tough, on-site performance that resists 6-foot drops, 250-lb crushes and military-grade shocks
- Go where the work is with a compact and lightweight (1.2lbs) design. Wearable. Attachable. Portable.
- Take on a variety of jobs with 90+ cartridges and 12 material types
- In a hurry to get started? Get the M211 Label Printer with Accessories Kit (M211-KIT). It includes: M211 Label Printer, M21-750-499 Label Cartridge, Quick Start Guide, AC Adapter, Belt Clip, Power Brick, Hard Case and Magnet.

## Specifications

Key Characteristics	Product Number	170380
	UPC	888434587515
	UOM	Each
	Trade Name	M211
	Brand Name	Brady®
	Country of Origin	Malaysia
	HTS Code (Harmonized Tariff Schedule)	8443.32.1050
	ECCN (Export Commodity Control Number)	EAR99
Dimensions	Dimensions	4 in H x 5.4 in W x 2.6 in D
	Height	4 in
	Width	5.4 in
	Depth	2.6 in
	Weight	1.2 lb

Material Characteristics	Color	Yellow, Black
Product Features	Application	Data and Telecommunications Labeling, Electrical Labeling, General Identification, Lean and 5S Labeling, Warehouse Marking, Wire and Cable Labeling
	Shipped With Battery	Yes
	How Is Battery Shipped	Shipped installed in equipment
	Battery mAh Rating	1200 mAh
	Built-In Label Wizards	Breaker Box, Flags, General, Patch Panel, Pipe Marker, Safety, Terminal Block, Wire Wrap
	Connectivity Options	Bluetooth® 5 Low Energy (class II)
	Cutter Type	Auto Cutter, With label retention
	Display Type	None
	Keyboard Type	None
	Memory	Memory via connected mobile device
	Stand Alone Printing	Mobile device connected
	Number of Symbols	Dependant on software
	Plug Type	US
	Power Supply Voltage	110 - 240 V
	Auto Shut-Off / Power Conserve	User Configurable, Yes
	Recharge Time	4 hours
	Special Characters Quantity	Determined by software
	User Interface Type	Mobile device

	Battery Type	Internal, not removable, Lithium-ion Battery
Printing Specifications	Barcode Symbologies - 2D	Data Matrix, PDF417, QR code
	Barcode Symbologies - Linear	Code 128, Code 128A, Code 128B, Code 128C, Code 39, Code 39 Full ASCII, Code 93, Code 93 Full ASCII, EAN-13, EAN-13 Extension 2, EAN-13 Extension 5, EAN-8, EAN-8 Extension 2, EAN-8 Extension 5, GS1-128, HIBC, Interleaved 2 of 5, JAN-13, JAN-8, UPC-A, UPC-E
	Calibration Required?	Automated through Smart Cell
	Color Printing Capability	Single Color
	Font Sizes	4 - 150 pt
	Font Styles	Determined by software
	Label Retention Feature	Yes
	Maximum Labels per Day	100
	Maximum Print Speed	0.6 in/s
	Print Resolution	203 dpi
	Print Technology	Thermal Transfer
	On Screen Indicators	Battery Life, Bluetooth Status, Error Messaging
	Device Indicators	Bluetooth indicating lights: pulsing blue = broadcasting signal; solid blue = device connected or paired, Error indicating lights: pulsing orange = error, Power indicating lights: solid green = 51-100% battery life; solid orange = 21-50% battery life; solid red = 11-20% battery life; flashing

		red = 1-10% battery life; flashing green = charging
	Device Drop Test & Durability	Resistant to 250-lb crushes, Resistant to 6-foot drops, Resistant to military-grade shocks (MIL-STD-810G)
Compatibility	Compatible Media	M21-
	Label Material Types	Heat-shrink Polyolefin, Nylon Cloth, Paper, Polyester, Polypropylene, Self-laminating Polyester, Self-laminating Vinyl, Vinyl
	Continuous & Die-Cut Materials Supported	Continuous and Die-cut
	Custom Media Parts Available	No
	Custom Labels Available	No
	Maximum Label/Tape Width	0.75 in
	Maximum Print Width	0.62 in
	Maximum Printed Label Length	36 in
	Maximum Liner Width	0.875 in
	Phones & Tablets Supported	Android devices with Android OS 5+, iPhone 5S or newer with iOS 10+
	Software Compatibility	Express Labels Mobile App
	Languages Available	Bahasa (Indonesian), Bahasa Malay, Bulgarian, Chinese (Traditional and Simplified), Croatian, Czech, Danish, Dutch, English (US), Estonian, Finnish, French (France), German, Hungarian, Italian, Japanese, Korean, Norwegian, Polish,

		Portuguese (Portugal), Romanian, Russian, Slovak, Slovenian, Spanish (universal), Swedish, Thai, Turkish, Vietnamese
What's Included	Includes	(1) AC Adapter (North America), (1) M211 Printer, (1) M21-750-499 Label Cartridge, (1) Quick Start Guide
	Warranty (North America)	2 Years
Compliance	UNSPSC	45101520
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863