



[Home](#) / [Printers and Scanners](#) / [Printers by Application](#) / [Electrical Printers](#) /

M210 Handheld Label Maker with Accessory Kit

M210 Handheld Label Maker with Accessory Kit



M210 Handheld Label Maker with Accessory Kit

[Overview](#) [Specifications](#) [Support](#) [Related Items](#)





Product Highlights

Maximum Label/Tape Width: 0.75 in

Color Printing Capability: Single Color

Maximum Labels per Day: 100

Stand Alone Printing: Stand-alone

Print Resolution: 203 dpi



Print Technology: Thermal Transfer

Part Number: M210-KIT

CONTACT US

Overview

Optimize on-site efficiency with the M210 Label Printer Kit. Everything you need to create fast, reliable and pre-sized labels.

- Clearly identify of wires, panels, circuit boards and other industrial items with accuracy and ease
- Label smarter and easier in low-lit areas with a backlit LCD graphics display and intuitive keypad contains letters A to Z and numbers 0 to 9
- Get more options to get more done across a variety of applications with 6 different text sizes ranging from 6 point to 40 point in a single color






- Ultimate flexibility and versatility across a wide range of uses with 90+ cartridges (continuous tape and pre-sized labels) and 12 different material types
- Meet tough and demanding work environments with enhanced durability – drop-tested and reinforced with molded rubber impact bumpers
- Get more done with more than 100 symbols including electrical, safety, and datacom
- Kit comes with: M210 Label Printer, AC Adapter/Battery Charger, M21 Series Nylon Cloth Patch Panel and Wire and Cable Labels, Li-Ion Rechargeable Battery, Quick Start Guide, Replacement Power Cord, and Hard Case

Specifications

Key Characteristics

Product Number	152263
UPC	888434559505
UOM	Kit
Trade Name	M210
Brand Name	Brady®



Country of Origin 	Malaysia
HTS Code (Harmonized Tariff Schedule) 	8443.32.1050
ECCN (Export Commodity Control Number) 	EAR99

Dimensions




Dimensions	9.5 in H x 4.5 in W x 2.5 in D
Height	9.5 in
Width	4.5 in
Depth	2.5 in
Display Size	2 x 1 in
Weight	1.653 lb

Material Characteristics


Color	Yellow, Black
-------	---------------





Product Features


Application 	Data and Telecommunications Labeling, Electrical Labeling, General Identification, Lean and 5S Labeling, Warehouse Marking, Wire and Cable Labeling
Shipped With Battery	Yes
How Is Battery Shipped	Shipped in box, not installed
Battery Weight (metric)	0.21 lb
Built-In Label Wizards	Flags, Patch Panel, Terminal Block, Wire Wrap
Connectivity Options 	None
Cutter Type	Single Hand Manual Actuate, Straight Cut, With label retention
Display Type	Monocolor LCD Screen
Keyboard Type	ABC
Memory	16 MB (2 MB available for storage, stores 12 labels)
Stand Alone Printing 	Stand-alone
Number of Symbols	193





Plug Type	US
Power Supply Voltage	110 - 240 V
Auto Shut-Off / Power Conserve	10 minutes
Recharge Time 	2.5 hours
User Interface Type	ABC Keypad
Battery Type	Optional AA Battery, Rechargeable Lithium-ion Battery


Printing Specifications

Barcode Symbolologies - 2D	Data Matrix, QR code
Barcode Symbolologies - Linear	Code 128, Code 39
Calibration Required? 	Automated through Smart Cell
Color Printing Capability	Single Color
Font Sizes	6 - 40 pt
Font Styles	Brady Standard Font
Label Retention Feature 	Yes



Maximum Labels per Day 	100
Minimum Label Length 	0.915 in
Maximum Print Speed	0.393 in/s
Minimum Liner Width	0.453 in
Print Resolution	203 dpi
Print Technology	Thermal Transfer
On Screen Indicators	Battery Life, Ribbon and label part number recognition, Ribbon Remaining, Supply Remaining
Device Drop Test & Durability	Resistant to 6-foot drops

Compatibility

Compatible Media 	M21-
Label Material Types	Heat-shrink Polyolefin, Nylon Cloth, Paper, Polyester, Polypropylene, Self-laminating Polyester, Self-laminating Vinyl, Vinyl
Continuous & Die-Cut Materials Supported	Continuous and Die-cut
Custom Media Parts Available	No




Custom Labels Available	No
Maximum Label/Tape Width	0.75 in
Maximum Print Width	0.63 in
Maximum Printed Label Length	36 in
Maximum Liner Width	0.875 in
Languages Available	Croatian, Czech, Danish, Dutch, English (US), Estonian, Finnish, French (France), German, Hungarian, Italian, Norwegian, Polish, Portuguese (Portugal), Romanian, Slovak, Slovenian, Spanish (universal), Swedish, Turkish

What's Included

Includes	(1) AC Adapter/Battery Charger (M210-AC), (1) Hard Case (M210-HC), (1) Li-ion Rechargeable Battery (M210-BATTERY), (1) M21 Series Nylon Cloth Patch Panel and Wire and Cable Labels (M21-750-499), (1) Quick Start Guide, (1) Replacement Power Cord - North America, (1) M210 Label Printer (M210)
Warranty (North America)	2 Years

Compliance



UNSPSC 	45101520
Patent Number(s)	6.604.874;6.732.619;US 8.322.939
RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863

Related Items



Soft Case for BMP51,
M210, M211, BMP21-
PLUS Printers

Soft Case for BMP51, M210,
M211, BMP21-PLUS Printers

BMP-SC-1



Support

LITERATURE

M210 Info Sheet
M210 and M210-LAB Portable
Label Printer Quick Start Guide

M210 and M210-LAB User Manual

Portable Printer Brochure
Portable Printer Brochure

SHOW MORE

