

**PLUG AND PLAY STRIP IP65 5M RGB 7.2W/M 30LED/M 10MM WIDTH 115 BEAM BLISTER WITH IR CONTROLLER AND IP20 UK PLUG ADAPTOR
INTEGRAL**

ILSTRGBA081B



Effortlessly transform your room with Integral LED's Plug and Play Colour Changing Strip Kit. This convenient package comes with 5 metres of strip, a driver and a remote control. The ideal decorative lighting retail product.

Details

Quick Order Code:	582543
Barcode:	5055788235293
Category:	Strips
Range Name:	Plug and Play Strip
Product Type:	Colour strip
Market Segment:	Commercial indoor, Residential indoor
Features:	Plug and Play - colour changing
Warranty (Years):	2
CE RoHS:	Yes

Physical Data

Product Width (mm):	10
Product Weight (g):	390
Strip Cut Points (mm):	100
Max Run Length (m):	5
Placement / Application:	Decorative indoor
Strip length (M):	5
Strip Width (mm):	10

Electrical Data

Power Consumption (w):	7.2
Voltage (V):	12
Watts per metre:	6.1w - 10w
Output Voltage (V):	DC
Dimming:	Dimmable
EN:	IEC 62031, IEC 60598-1
LVD Certified:	Yes

Light Data

Colour Temperature Name:	RGB
Beam Angle:	120
Colour Type:	RGB
LED Size (mm):	5050
LED Type:	Surface mounted device (SMD)
LEDs per meter:	30
Lifetime (hours):	15000
Reel Length (m):	5

Environment

EN:	IEC 62031, IEC 60598-1
LVD Certified:	Yes
CE RoHS:	Yes
Hg 0% (Mercury Free):	Yes
IP Rating (Ingress Protection):	IP20
Lowest Operating Temperature (°C):	-25
Maximum Operating Temperature (°C):	50

Packaging

Package Weight (g):	405
Package Length (mm):	220
Package Width (mm):	73
Package Depth (mm):	280