

TDC600


British plug top fuse fast-acting



Product features

- 1/4" x 1" fast-acting, high breaking capacity fuse.
- Ceramic tube - end caps: silver-plated copper.
- High breaking capacity
- 600 Vac
- Standards BS1362
- UL recognized

Dimension-mm



Electrical Ratings (Part number and Amperes)

600 Vac


TDC600-2A

TDC600-10A

Rated Current	Rated Voltage (V)	Breaking Capacity	Power Dissipation (W)	Color	Approvals
2A	600	200A,600V	1 Watt @ Rated Current	Blue	Asta, BSI
10A		10kA, 250V p.f. 0.7 - 0.8			

Limits for Pre-arcing Time

In	1.0 In.	1.6 In.	1.9 In.
	MIN	MIN	MAX
2A, 10A	1000 hours	30 min.	30 min.



Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 2081 SB98107
June 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.