



Rampmat

A popular honeycomb mat for all environments



- A popular choice of doormat, suitable for most climates.
- The raised honeycomb design provides grip while scraping away dirt and moisture.
- Moulded bevelled edging for trip-resistance and wheeled access.
- Manufactured from durable rubber.
- Slip tested to DIN 51130.



Parts

Part Number	Size	Colour	Weight (kg)
RP010001	0.9 m x 1.5 m	Black	8
RP010002	0.8 m x 1.2 m	Black	5

Technical Specifications

Material	Rubber mix, including >50% recycled material
Surface Finish	Raised circular surface
Product Height	14 mm
Min. Operating Temperature	-20°C
Max. Operating Temperature	+130°C
Environmental Resistance	Suitable for wet and dry environments, indoors or outdoors
Typical Applications	General industrial, Areas where swarf is prevalent. Entrance areas.

Installation Method	Loose lay
Cleaning Method	Wash with cold water, use vacuum cleaner or use pressure pump to remove dirt
COO (Country of Origin)	IN
Tensile Strength	2.75 to 3.25 MPa
Notes	Silicone is used in the production process of the mats and a residue will possibly be left on the mat
Slip Tested to	DIN 51130 - R10

Additional Information



Rampmat Ramp Slip Test DIN 51130

Get in touch | To order FREE samples or arrange a site visit please call +44 (0)1788 228 555 or email sales@cobaeeurope.com

www.cobaeeurope.com