

Eaton molded case circuit breaker accessory line and load terminal

T300K

UPC:786679511930

Dimensions:

- **Height:** 1.2 IN
- **Length:** 2.2 IN
- **Width:** 1.6 IN

Weight:.25 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Terminal
- **Amperage Rating:** 225A
- **Wire Size:** #3 AWG-350 kcmil Cu
- **Series:** Series C
- **Terminals:** Pressure type line and load

Supporting documents:

- [Application of Tap Rules to Molded Case Breaker Terminals](#)
- [UL listed 100%-rated molded case circuit breakers](#)
- [Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)
- [Multi-wire lugs product aid](#)
- [Current limiting Series C molded case circuit breakers product aid](#)
- [Power metering and monitoring with Modbus RTU product aid](#)
- [Circuit breaker motor operators product aid](#)

- [Plug-in adapters for molded case circuit breakers product aid](#)
- [StrandAble terminals product aid](#)
- [Motor protection circuit breakers product aid](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Molded case circuit breakers](#)
- [Breaker service centers](#)
- [MOEM MCCB product selection guide](#)
- [Series C G-Frame molded case circuit breakers time current curves](#)
- [Series C F-Frame molded case circuit breakers](#)
- [Series C J-Frame molded case circuit breakers time current curves](#)
- [Eaton Specification Sheet - T300K](#)

Certifications:

- [UL Listed](#)

Product compliance:

- [Contact Manufacturer](#)