



04101006

Aluminium Enclosure Aluform

100 x 100 x 61 mm

Aluminium Enclosure Aluform 100 x 100 x 61 mm

[Catalogues](#)
[Assembly instructions](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	100 mm
Width	100 mm
Depth	61 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	130 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	0.4
GTIN	4250157901095

ETIM classification

ETIM 8 EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



04000010

Aluform External hinges



04000020

Aluform Lid safety strip



04000100

Aluform External mounting bracket 100



10011031

Mounting plate for 04.101006



10061007

DIN rail 15 for 01.101008



10061471

DIN rail 35/7,5 for 04.101006