




04142207

Aluminium Enclosure Aluform

140 x 220 x 72 mm

Aluminium Enclosure Aluform 140 x 220 x 72 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)[Assignmentplan](#)[Terminal Mounting](#)

Technical data

Height	140 mm
Width	220 mm
Depth	72 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	130 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	1.25
GTIN	4250157901163

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



04000010

Aluform External hinges



04000020

Aluform Lid safety strip



04000140

Aluform External mounting bracket 140



10011036

Mounting plate for 04.142207



10061046

DIN rail 15 for 04.142207



10061476

DIN rail 35/7,5 for 04.142207