

AXIS IV MKII

4x32W RGBW LED 4 Head Beam Moving Head

When giving colors to your gigs passes through simplicity of use, portability and the benefits of modern LED technology, AXIS IV MKII becomes the reference to all musicians, DJs and entertainment operators. AXIS IV MKII has been designed to be all-in-one system. This bar offers 4 moving heads able to swivel by up to 540° horizontally and 270° vertically, with extremely fast and accurate movements. It can be mounted on a truss and on lighting supports with Ø35mm pole, thanks to the supplied adapter. Each moving head mounts a 32W RGBW 4in1 LED with beam angle from 6° which ensures brilliant colors, high performance in terms of brightness and duration. Each head, also, can be controlled independently both in PAN/TILT movements and colors. Control modes are Sound, DMX Master/Slave, and Auto. It is also available (optional) a professional flight case with wheels (2 with brake) for two bars (AXIS IV MKII CASE – SKU: J684J).

€ 941,00

including VAT



KEY FEATURES

Bar with four-head LED moving light (4pcs 32W RGBW 4in1)

Easy to control by LCD Graphic Display

6° Beam Angle

Light Lumen @1m from 24000 to 68000 LUX

Standalone Operation

Sound Control via built-in microphone

Master/Slave synchronization

DMX-512 protocol with 5 channel modes (6CH, 10CH, 19CH, 32CH and 56CH DMX)

2 bundled Fast lock Omega Brackets

Bundles Ø36mm Stand Adapter (stand not included)

MORE SPECIFICATIONS

Light source	4x 32W RGBW 4in1 LED
Brightness @ 1m (single head)	R 24000 Lux; G 50000 Lux; B 80000 lux; W 68000 lux
Brightness @ 2m (single head)	R 11500 lux; G 18000 Lux; B 27000 Lux; 26000 lux
Colors	RGBW with color mixing
Beam corner	6°
Control mode	DMX512, Master / Slave, Sound, Auto
DMX mode	6CH / 10CH / 19CH / 32CH / 56CH
Power connectors	PowerCon input / output
DMX connectors	In/Out XLR 5-Pin + In/Out XLR 3-Pin
Display	2.4 "TFT LCD
Power supply	110V ~ 240V - 50-60Hz
Max Power Consumption	200W
Fuse	F3AL / 250V (5x20mm)
Bar size (WxDxH)	1003.6 x 115 x 271.4 mm
Bar weight	11.5 kg
Packaging dimensions (WxDxH)	1090 x 180 x 360 mm
Packaging Weight	13.25 kg
Accessories supplied	1x power cable, 2x quick-lock omega-type brackets, Ø36mm pole adapter (stand not included)