

PRODUCT-DETAILS

OT40F4C

OT40F4C CHANGE-OVER SWITCH



General Information	
Extended Product Type	OT40F4C
Product ID	1SCA104934R1001
EAN	6417019390741
Catalog Description	OT40F4C CHANGE-OVER SWITCH
Long Description	OT40F4C CHANGE-OVER SWITCH, Handle and shaft need to be ordered separately, Open transition

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country of Origin	Finland (FI)

Popular Downloads	
Data Sheet, Technical Information	1SCC303003C0201
Instructions and Manuals	1SCC301054M0006

Dimensions	
Product Net Width	96 mm

Product Net Height	68 mm
Product Net Depth /	68 mm
Length	
Product Net Weight	96 lb
	0.31 kg

Technical	
Rated Operational Current AC-21A (I _e)	(380 415 V) 40 A (500 V) 40 A (690 V) 40 A
Rated Operational Current AC-22A (I _e)	(380 415 V) 40 A (500 V) 40 A (690 V) 40 A
Rated Operational Current AC-23A (I _e)	(380 415 V) 23 A (500 V) 23 A (690 V) 12 A
Rated Operational Power AC-23A (P _e)	(380 415 V) 11 kW (500 V) 11 kW (690 V) 11 kW
Conventional Free-air Thermal Current (I _{th})	q = 40 °C 40 A
Conventional Thermal Current (I _{the})	Fully Enclosed 40 A
Rated Impulse Withstand Voltage (U _{imp})	8 kV
Rated Insulation Voltage (Ui)	750 V
Rated Operational Voltage	750 V
Rated Short-time Withstand Current Low Voltage (I _{cw})	for 1 s 0.5 kiloampere rms
Power Loss	1.6 W
Pollution Degree	3
Handle Color	Black
Handle Type	Handle and shaft not included
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
	Mechanism on Top of the Switch
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out, Bottom In - Top Out
Operating Mode	Front operated
Mounting Type	Base mounting
Number of Poles	4
Cable Cross-Section	0.75 10 mm²
Degree of Protection	Front IP20
Transition Type	Open

Technical UL/CSA	
Horsepower Rating	(acc. to UL 200 V) 10 Hp
UL/CSA	(acc. to UL 480 V) 20 Hp
	(acc. to UL 240 V) 10 Hp
	(acc. to UL 208 V) 10 Hp
	(acc. to UL 600 V) 25 Hp
Ampere Rating UL/CSA	40 A

Certificates and Declarations (Document Number)	
Declaration of	1SCC303019D0201
Conformity - CE	
Instructions and	1SCC301054M0006
Manuals	
RoHS Information	1SCC301183D0201

Container Information	
Package Level 1 Units	1 piece
Package Level 1 Width	80 mm
Package Level 1 Depth / Length	108 mm
Package Level 1 Height	79 mm
Package Level 1 Gross Weight	0.76 kg
Package Level 1 EAN	6417019390741

Classifications	
Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnector
ETIM 6	EC000216 - Switch disconnector
ETIM 7	EC000216 - Switch disconnector
ETIM 8	EC000216 - Switch disconnector
UNSPSC	39122233
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3601443

Categories

 $Low\ Voltage\ Products\ and\ Systems \rightarrow Switches \rightarrow Change-over\ and\ Transfer\ Switches \rightarrow Manual\ Change-over\ Switches$

