



# Wall-Mounted Open Box 12U W600 D400 Fixed 19" Plain Door R7035

NSYOPB12U4FR

Range	Actassi
Product name	Actassi OPB
Product or component type	19" enclosure
Device application	Cabling
Applications	To protect network connectivity equipment To mount 19" equipment To improve security of the equipment
Enclosure type	Open box
Support equipment	2 x fixed 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Plain door
Door type	Front plain door - with 1 point locking system (key: 333) - reversible opening at 180 $^{\circ}$
Accessibility for operation	Side Front Rear
Removable parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless
Colour	Light grey (RAL 7035)

#### Complementary

<del>complementally</del>	
Device composition	3 x cable entries 2 x panels side 2 x 19" uprights front 1 x open structure 1 x plain door front
Load rating	50 kg static 3 kg by unit
Back face	Cut-out
Side face	Panel
Number of cut-out	1 cut-outside 1 cut-outbottom 1 cut-outtop
Installation mode	Wall mounted
Material	Sheet steel: structure Sheet steel: door

Galvanized steel: upright

Surface finish	Epoxy-polyester powder	
Width	600 mm	
Height	650 mm	
Depth	400 mm	
Net weight	22 kg	
Number of rack unit	12U	
Targeted region	Europe	

#### **Environment**

IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	IEC 60297-3-100 EIA-310D

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	21.0 kg
Package 1 Height	86.7 cm
Package 1 width	47.0 cm
Package 1 Length	61.5 cm
Unit Type of Package 2	P12
Number of Units in Package 2	6
Package 2 Weight	144.0 kg
Package 2 Height	156.0 cm
Package 2 width	100.0 cm
Package 2 Length	120.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

### **Contractual warranty**

Warranty 18 months