



infrastructure for a connected world

PRODUCT CHANGE NOTIFICATION

Product Category TERMINALS 20220809-1

Product Group TERMINALS AND REELSMART

ISSUE DATE: ☒ NA ☒ MEA ☒ AP-Aug-22

☒ DISCONTINUATION ☒ LATAM

IMPACTED REGIONS: ☐ OTHER

REASON FOR CHANGE:

DESCRIPTION OF CHANGE: (Required)

Panduit has made the decision to obsolete select Pan-TermTM and ReelSmartTM terminal profiles and/or packaging options. For further details, please refer to the "Part Numbers" tab below. For further help understanding these changes or Panduit's total product offerings, please reach out to your local sales representative, or contact our customer service team.

Photos/Drawing (where applicable)

IMPACTED PART NUMBERS AND REPLACEMENT PART NUMBERS: (where applicable)

[Reference Page 2 / Linked PDF](#)

DATES: DISCONTINUATION AND NEW PRODUCT AVAILABILITY:

SCHEDULE FOR CHANGE	Year (YYYY)	Month (MM)	Day (DD)
New product sample availability date			
Old product discontinuation date*	2022	11	28

***Important:** A return material authorization (RMA) may be obtained for these affected part numbers and they may be returned up to 60 days after the product discontinuation announcement date if purchased within the last 18 months and subject to the return policy requirements outlined in Panduit's Authorized Distributor Policy. Please contact your local Panduit Customer Experience team if you have any questions.

CUSTOMER SERVICE CONTACTS

ASIA PACIFIC	AUSTRALIA: 1-800 7263848 AUS-CSVM@panduit.com	CHINA: 400-820-1900 CHN-CustomerService@panduit.com	HONG KONG: 800-965768 CHN-CustomerService@panduit.com
	INDIA: 000 800 6501844 (Fixed) 000 800 6500369 (Mobile) SGP-Customer_Service@panduit.com	INDONESIA: 001 803 65 7571 SGP-Customer_Service@panduit.com	JAPAN: +81-3-6863-6000 JPN-CS@panduit.com
	KOREA: 02-2182-7300 KOR-CustomerService@panduit.com	MALAYSIA 1800 801435 SGP-Customer_Service@panduit.com	SINGAPORE: 1-800-7263848 SGP-Customer_Service@panduit.com
	TAIWAN: 0080 165 1487 SGP-Customer_Service@panduit.com	THAILAND: 001-800-65-6385 SGP-Customer_Service@panduit.com	
LATIN AMERICA	BRAZIL 08000562613 (Toll Free) BRA-custservice@panduit.com	MEXICO: +52-33-37776000 x80520 01 800 360 86 00 (Toll Free) MEX-customerservice@panduit.com	OTHER LA COUNTRIES: Phone USA 1-708-532-1800 TP-CS-INTERNATIONAL@panduit.com
NORTH AMERICA	USA & CANADA: 1-800-777-3300 cs@panduit.com	EMEA	EMEA: +44 208 6017219 EMEA-CustomerServices@panduit.com

To add a contact or to unsubscribe, please send an email to:

PCN@panduit.com

IMPACTED PART NUMBER(s)	Replacement Part 1	Replacement Part 2	IMPACTED PART NUMBER(s)	Replacement Part 1	Replacement Part 2
BS22-C	BS22-M		PV10-10F-E	PV10-10F-L	
BSH14-D	BSH14-Q		PNF18-10F-C	PN18-10F-C	
BSK14-M	BS14-C		BSV10X-E	BSV10X-D	
PN18-14F-C	PN18-14R-C		DNFR14-205B-M	DNFR14-205B-L	
DR18-205-C	DNFR18-205B-M		DR14-250-C	DR14-250-M	
DVF18-250-CY	DVF18-250-MY		PN14-10LF-3K	PNF14-10LF-3K	
P10-8LF-L	PV10-8LF-L	PN10-8LF-L	DVF14-188-M	DV14-188B-M	
PN14-10FF-M	PN14-10FF-C		P10-14RHT6-D	P10-14RHT6-L	
P4-12R-T	P4-56R-T		DNG18-188FB-3K	DNF18-188FIB-3K	
PV2-12R-XY	PV2-38R-XY		DNG18-187FB-C	DNF18-187FIB-C	
PN14-6RX-C	PNF14-6R-M		DNG14-187FB-L	DNF14-187FIB-C	
P18-12R-C	PV18-12R-LY		DNG14-188FB-L	DNF14-188FIB-C	
D-250A-M	D-250A-C		PNF10-38R-D	PNF10-38R-L	
PV14-4RX-C	PV14-4R-M		PV18-8LFX-MY	PV18-8LF-MY	P18-8LF-M
PV14-10FF-C	PV14-10FF-M		PNF14-8F-3K	PN14-8F-3K	
PV18-10LFX-CY	PV18-10LF-CY		DNG14-250FB-L	DNG14-250FB-M	
PV18-6FF-CY	PV18-6F-CY		PN18-10FN-C	PN18-10F-C	
PV4-12R-E	PV4-56R-E		P10-6F-L	P10-6R-L	PV10-6F-L
PV8-12RX-TY	PV8-38R-TY		DNG14-187FB-3K	DNF14-187FIB-3K	
DV14-188B-C	DV14-188B-M		PN12-56HDR-L	P12-56HDR-D	PV12-56HDRB-2K
PV18-6FN-CY	PV18-6FN-MY		DNG14-188FB-3K	DNF14-188FIB-3K	
P2-12R-T	P2-38R-T		P8-12R-Q	P8-38R-Q	
PN18-10LF-M	PNF18-10LF-C		PNF18-10LF-M	PNF18-10LF-C	
PV14-P47-E	PV14-P47-C		PNF10-10FF-2K	PN10-10FF-2K	
P14-6F-C	P14-6F-M		DNFR18-206B-L	DNFR18-206B-M	
PN12-10HDR-L	PN12-10HDR-D		PNF10-8LF-L	PN10-8LF-L	
BSV18X-E	BSV18X-LY		PN14-6FN-C	PN14-6FN-M	
PV10-8FX-L	PV10-8FX-D		P18-8RHT6-M	P18-8RHT6-C	
PNF10-8FF-2K	PNF10-8LF-2K		PNF14-6FN-3K	PN14-6FN-M	

DPF14-206FIB-M	DNF14-206FIB-M		DPF14-206FIB-3K	DNF14-206FIB-3K	
PN14-14RX-L	PNF14-14R-C		PNF10-8F-D	PN10-8F-D	PNF10-8R-D
PV14-8FF-C	PV14-8FF-M		DNF18-205-C	DNF18-205FIB-M	
P18-6RN-M	P18-6R-M		PV18-6LFX-MY	PV18-6LF-MY	P18-6LF-M
PV6-38R-X	PV6-38R-T		PV12-38HDR-D	P12-38HDR-D	
PV12-14HDR-L	PN12-14HDR-D		PV14-6LFX-C	PV14-6LFX-M	P14-6LF-C
PV12-10HDR-L	PN12-10HDR-D		BSP18-3K	BSN18-3K	
DNFR14-205FIB-L			PV14-6LFW-M	PV18-6LF-MY	
PN14-10LFN-C	PN14-10LFN-M		P14-8FF-C	P14-8FF-M	
DV18-250MB-MY	DV18-250MB-CY		PN18-10FN-3K	PN18-10F-3K	
PN14-6LF-3K	PNF14-6LF-3K		DPF18-111FIB-C	DNF18-111FIB-C	
PN18-38R-M	PN18-38R-C		DPF18-250FIB-C	DPF18-250FIB-M	
PN18-6F-3K	PNF18-6F-3K		PN14-6RN-3K	PNF14-6RN-3K	
PN10-56R-2K	PNF10-56R-2K		PV12-6HDR-D	PN12-6HDR-D	
PV18-38R-MY	PV18-38R-LY		DNF18-250M-M	DNF18-250M-C	
PN14-10F-3K	PNF14-10F-3K		PV8-12R-XY	PV8-38R-TY	
PNF14-38R-L	PN14-38R-L		DNF14-250M-M	DNF14-250M-C	
P18-P47-C	P18-P47-M		DPF10-250FI-D	DNF10-250FI-L	
PV6-56R-X	PV6-56R-T		PNF18-6LF-C	PN18-6LF-M	
DPFR18250FIB-KD	DNFR18250FIB-KD		PV2-14R-TY	PV2-14R-XY	
PV14-8LFX-C	PV14-8LF-C	P14-8LF-M	PV10-56RX-L	PN10-56RX-L	
PV14-14RX-L	PV14-14RX-M		P2-14R-X	P2-14R-T	
PV6-12R-X	PV6-56R-T		PN10-38RX-L	PV10-38RX-L	PN10-38R-L
PNF14-14F-C	PN14-14F-C		P2-38R-X	P2-38R-T	
P14-10F-M	P14-10F-C		PN14-6FF-3K	PNF14-6FF-3K	
PN10-8F-2K	PNF10-8F-2K		DPF14-205FIB-M	DNF14-205FIB-M	
P14-6LF-M	P14-6LF-C		PNF14-4R-3K	PV14-4RB-3K	
PN10-6R-2K	PNF10-6R-2K		P4-12R-E	P4-56R-E	
P10-10LF-D	PN10-10LF-D	PV10-10LF-D	DNF18-188-M	DNF18-188-C	
PN10-6LF-L	PN10-6LF-D		DPF18-206FIB-M	DNF18-206FIB-M	
P10-8LF-D	PV10-8LF-D	PN10-8LF-D	PN14-12R-Q	P14-12R-L	PV14-12R-L

PN18-8FF-C	PN18-8FF-M		DPF14-187FIB-3K	DNF14-187FIB-3K	
P14-8RHT6-M	P14-8RHT6-C		DNF18-187-M	DNF18-187-C	
DPF18-110FIB-C	DNF18-110FIB-C		DNH14-250FIB-Q	D14-250-C	HSTT12-CC
P4-10R-E	P4-10R-T		PV18-10FN-CY	P18-10FN-C	
PN10-8RX-L	PV10-8RX-D	PNF10-8R-L	PN18-10FF-M	PN18-10F-C	
PN14-6FF-C	PN14-6FF-M		DNH18-250FIB-Q	D18-250-C	HSTT09-CC
P10-8F-L	P10-8F-D		PV14-56RX-L	PV14-14RX-M	PV14-56R-C
P18-6FN-M	P18-6FN-C		PK6-14R-T	P6-14R-T	
PV8-12R-TY	PV8-38R-TY		PMNF1-5F-C	PNF18-10F-C	
P8-12R-T	P8-38R-T		DVF14-250-M	DVF14-250-C	
PV14-8LFX-M	PV14-8LF-M	P14-8LF-M	PV14-10LFX-C	PV14-10LF-C	P14-10LF-M
PV10-10FX-L	PV10-10FX-D		PNF18-14F-C	PNF18-14R-C	
DPF10-250FIB-L	DNF10-250FIB-L		PV10-8RX-L	PV10-8RX-D	
P2-56R-X	P2-56R-T		P8-8RNHT6-Q	P8-8R-Q	
PV4-10R-E	PV4-10R-T		PV10-8LFX-L	PV10-8LF-L	
P18-6F-C	P18-6F-M		PNF10-6F-2K	PV10-6FB-2K	PN10-6F-D
DNH14-250FIM-Q	D14-250MB-M		P4-38RHT6-E	P4-38R-E	
DNH18-250FIM-Q	D18-250MB-M		PN18-6RN-3K	PN18-6R-3K	
P2-12R-X	P2-38R-T		DPF18-111FIB-M	DNF18-111FIB-M	
P14-6RHT6-M	P14-6RHT6-C		PV10-14FX-L	PV10-14F-L	PV10-14RX-L
PN18-10F-M	PN18-10F-C		DV18-187B-CY	DVF18-187-MY	
PN18-10LF-C	PNF18-10LF-C		DNFR18-205B-L	DNFR18-205B-M	
PV14-4R-C	PV14-4R-M		P6-12R-T	P6-56R-T	
PV6-10RX-X	PV6-10RX-T		DPF18-187FIB-3K	DNF18-187FIB-3K	
PK6-10R-T	P6-10R-T		PV10-8F-E	PV10-8F-L	
PV4-12R-T	PV4-56R-T		DNF14-187-M	DNF14-187-C	
P14-P47-C	P14-P47-M		PN18-14F-M	PN18-14R-M	
BSV14X-E	BSV14X-L		DPFR18205FIB-KD	DNFR18205FIB-KD	
PNF14-6LF-C	PNF14-6LF-M		DPF18-206FIB-C		
P8-8R-Q	P8-8R-T		PNF18-38R-M	PN18-38R-C	
DPF18-250FIM-L	DPF18-250FIM-M		DNF18-206-C		

PN10-14LF-L	PV10-14LF-L		PNF18-10F-3K	PN18-10F-3K	
PNF18-56R-M	PN18-56R-M		PN18-10LFN-C	PNF18-10LF-C	PN14-10LFN-M
PV18-4RNB-3K	PV18-4RB-3K		P2-14RHT6-X	P2-56RHT6-X	P2-14R-T
PV12-38HDRB-2K	P12-38HDR-D		DPF14-205FIB-3K	DNF14-205FIB-3K	
P8-14RHT6-Q	P8-14R-Q		PN14-6LFW-C	PN14-6LF-C	
PV14-8FX-C	PV14-8RX-M	PV14-8F-C	KP-F1	KP-FSD1	
PV8-56RX-QY	PV8-56RX-TY		KP-F2	KP-FSD2	
P18-10RHT6-C	P18-10RHT6-M		PN14-10FF-3K	PNF14-10FF-3K	
DNF14-206-C	DNF14-206FIB-C		DPF10-250FI-L	DNF10-250FI-L	
PV2-10R-XY	PV2-14R-XY	P2-10R-T	PV4-12RX-E	PV4-56R-E	
DPF18-205FIB-M	DNF18-205FIB-L		PV8-12RX-XY	PV8-38R-TY	
DPF18-110FIB-3K	DNF18-110FIB-3K		BSK14-L	BS14-C	
PN14-4R-C	PN14-4R-M		PV14-14FB-3K	PV14-14RB-3K	PN14-14F-C
PV10-10LFX-L	PV10-10LF-L		P22-4R-C	P22-4R-M	
PV18-10LFNB-3K	PV18-10LFB-3K		BSK10-D	BS10-D	
PN18-12R-L	PV18-12R-LY		PN22-6F-C	PN22-6F-M	
DNF14-205-C	DNF14-205FIB-C		PS16-C	PS16-M	
PN14-10FN-C	PN14-10F-C		PS18-C	PS18-M	
DPF18-205FIB-3K	DNF18-205FIB-3K		PSN16-C	PSN16-M	
PV18-10FFB-3K	PV18-10FB-3K		PSN18-C	PSN18-M	
DNFR18-205FIB-L	DNFR18-205FIB-M		PV22-2R-CYY	P22-2R-M	
P6-12R-E	P6-56R-E		SR2		