

Product data sheet

Specifications



Industrial control transformer,
Type T, 1 phase, 1000VA,
240/416/480/600V primary,
99/120/130V secondary, 50/60Hz

9070T1000D50

Product availability : Stock - Normally stocked in distribution facility

Price* : 1,446.00 USD

Main

Product Type	Industrial Control Transformer
Power Rating	1000 VA
Type	T

Complementary

Number of Phases	1 phase 1000 VA UL 1000 VA CSA 1000 VA NOM 630 VA
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	6.17 in (156.72 mm)
Width	7.06 in (179.32 mm)
Depth	5.92 in (150.37 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC23

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	16201-9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	785901398073
Number of Units in Package 1	1
Package 1 Weight	35.49 lb(US) (16.098 kg)

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	MX
Packing Units	
Unit Type of Package 1	PCE
Package 1 Height	6.70 in (17.018 cm)
Package 1 Width	8.20 in (20.828 cm)
Package 1 Length	8.60 in (21.844 cm)
Offer Sustainability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Contractual warranty	
Warranty	10 Years