



FRONT VIEW



SIDE VIEW



Click [here](#) for the 3D model.

Dimensions

D	22.5mm MAX
L	44mm MAX
LL	40mm +/-5mm
F	1mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	70

General Information

Series	C4G
Dielectric	Metallized Polypropylene
Style	Axial
Features	Switching
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Component Weight	15.3 g
Miscellaneous	Polyester Tape & Resin Protection.

Specifications

Capacitance	3 uF
Capacitance Tolerance	5%
Voltage AC	330 VAC
Voltage DC	600 VDC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	40 V/us
Resistance	4.8 mOhms (100kHz)
Ripple Current	9 Amps (100kHz 70C), 120 Amps (Peak)