

PHG.0T.304.CLLC45Z

SUMMARY

Wires

Low voltage



Image is for illustrative purpose only

Series	ОТ
Termination type	Female solder
IP rating	68
AWG wire size	30.00 - 22.00
Cable Ø	4.10 - 4.50 mm
Status	active
Matching parts	FGG.0T.304.CLAC45Z

4

Download

Request a quote Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model	PH*: Free receptacle, cable collet and nut for fitting a bend relief
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Variant	Z : Nut for fitting a bend relief
Weight	21.42 g
Performance	

Configuration	T.304:4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	7 Amps

Specifications

Contact Type: Solder Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in) Max. Solid Conductor: 0.34 mm² (AWG 22) Max. Stranded Conductor: 0.34 mm² (AWG 22) R (max): 6.1 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Ρ

Vtest (contact-contact): 850 V (AC), 1200 V (DC) Vtest (contact-shell): 700 V (AC), 1000 V (DC)

Others

Endurance (Shell): >3000 mating cycles Temp (min / max): -55°C / +200°C Humidity (max): <=95% [at 60 deg C /140 F] Resistance to vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding efficiency (min): 75 dB (at 10 MHz) Shielding efficiency (min): 40 dB (at 1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	А	L	
mm.	9	37	
in.	0,35	1,46	

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

4280	PVC	Black	
------	-----	-------	--

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.