

SUPPLIER'S MODEL NO. PDU8WAYC13		SPECIFICATION
Powercool 1U PDU Horizontal Type 8Way C13 Sockets On Off Switch 1.8m UK Plug	Branding	Powercool
	Colour	Black
	Output Connection	C13 (Female)
	Control option	Power Switch(On/Off)
	Protection	No
	Cable Connection	UK 3-Pin (Male)
	No of Outputs	8
	Power Rating	230V-250V/10A, 50/60Hz
	Maximum Power	2500W
	Dimensions of PDU	483X44.5X44.5mm
	Orientation	Horizontal
	Mounting Height	1U
	Plug Type	UK
	Cable Type	H05VV-F 3G1.5mm
	Cable Length	1.8M(Net length)
	Operating Temperature	-10°C - 45°C (14°F - 113°F)
	Storage Temperature	-20°C - 55°C (-4°F - 131°F)
	Operating Humidity	<=95%
	Storage Humidity	<=95%
	Carton Dimensions	510X110X55mm
	Net Weight (Kg)	0.85
	Gross Weight (Kg)	1