

INDUSTRIAL PT100 TEMPERATURE PROBE

A heavy duty, industrial probe with a tough, silicone rubber insulated lead



- Pt100, Class B, 4 wire
- Stainless steel rigid sheath
- 6mm diameter, 50mm and 100mm lengths
- 2 and 4 meter lengths, 4 core 7/0.2mm silicone rubber insulated lead
- Operating temperature -50°C to +200°C

Probe Dia mm	Probe Length	Lead Length	Lab facility Stock Code	Manufacturing Code
6	50mm	2m	XF-374-FAR	DRG 010632A
6	100mm	2m	XF-375-FAR	DRG 010632B
6	50mm	4m	XF-541-FAR	DRG 010632C
6	100mm	4m	XF-542-FAR	DRG 010632D