


## Datasheet

# Connector Panel Face-plates – Type SSPF - Face Plate panels to suit miniature and standard SSPF panel mount sockets with stainless steel mounting bracket


Miniature SSPF Panel (12 way shown):

suitable with Miniature SSPF Panel Sockets (not included):



Standard SSPF Panel (4 way shown):

suitable with Standard SSPF Panel Sockets (not included):



- Anodised Aluminium Face-plates
- Suitable with miniature & standard fascia panel mounting thermocouple sockets supplied with stainless steel mounting bracket
- Etch matt & satin anodised finish
- Both miniature & standard size panels available in 2, 4, 6 & 12 way options
- All panel types have 4 x 3.2mm fixing holes, positioned 5mm centre line from corners edges

Panel Size	No. of rows/holes	Width	Height	Thickness	order code
<b>Miniature</b>					
2 way	1 x 2	55mm	45mm	2mm	<b>XF-1749-FAR</b>
4 way	1 x 4	85mm	45mm	2mm	<b>XF-1746-FAR</b>
6 way	1 x 6	115mm	45mm	2mm	<b>XF-1748-FAR</b>
12 way	1 x 12	205mm	45mm	2mm	<b>XF-1747-FAR</b>
<b>Standard</b>					
2 way	1 x 2	69mm	66mm	2.5mm	<b>XF-1757-FAR</b>
4 way	1 x 4	107mm	66mm	2.5mm	<b>XF-1755-FAR</b>
6 way	1 x 6	145mm	66mm	2.5mm	<b>XF-1756-FAR</b>
12 way	1 x 12	259mm	66mm	2.5mm	<b>XF-1758-FAR</b>