

LTE700 WFAV 225

Art. Number 370580



LTE 700 WFAV 225 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

- Wolsey LTE 700 Masthead Amplifier Kit
- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 2 Output
- 10-25 dB Variable Gain
- Weatherproof Housing
- Fully screened enclosure

Technical Specifications

ORDER INFORMATION

EAN Number 5702663705807

CHARACTERISTICS

Max. Output level (@ -60dB IMD) | dBμV 97 dBμV

FREQUENCY RANGE

Band UHF
 Input 1 - frequency | MHz 470...694 MHz
 Input 1 - channels 21...48
 LTE protection @ 700Mhz

GAIN

Input 1 - gain | dB 10...25 dB
 Input 1 - noise figure | dB 3,1 dB

RETURN LOSS

Return Loss | dB 10 Typ dB

ELECTRICAL

Impedance | Ω 75 Ω

OPERATIONAL



Technical Specifications

DC Operating voltage VDC	12 VDC
DC Current consumption mA	100 mA

CONNECTORS

Number of inputs	1
Number of outputs	2

MECHANICAL

Colour	Black
Product Height mm	215 mm
Product Width mm	120 mm
Product Depth mm	60 mm
Packaging Height m	0.060 m
Packaging Width m	0.220 m
Packaging Depth m	0.120 m
Packaging Volume m3	0.002 m3
Net Weight kg	0.540 kg
Tara Weight kg	0.065 kg
Total Weight kg	0.605 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened