

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300621084](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower A-Size (7/8"-M22) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 14 AWG, Black TPE Cable, 4.0m (13.12') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family	Industrial Cordsets
Series	<a href="#">130062</a>
Connector End A	BradPower A-Size (7/8"-M22)
Connector End B	BradPower A-Size (7/8"-M22)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	<a href="#">BradPower Cordsets and Receptacles</a>
Product Name	BradPower A-Size
Protocol	FF
Region	Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78172556846

**Physical**

Cable Diameter	9.47mm (.373")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	425.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire Size AWG	14
Wire/Cable Type	TC-ER

**Electrical**

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number 114030K21M040G

**Reference - Drawing Numbers**

Sales Drawing SD-130062-023-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130062 Series](#)

This document was generated on 10/31/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**