

mobile heat MH5

UK including rechargeable 5.5Ah battery and charger

EAN 4007841 068356

Article number 068356



CE

Function description

Mobil. Fast. Powerful. Mobile heat MH5, the 18 V cordless hot air tool with flexible setting options. Temperatures from 50°C to 500°C, with 6 airflow rates (up to 300 l/min) for any application. Ready for use in less than 4 seconds. LCD display for a perfect overview and settings. 4 preset application-specific programmes – can be changed at any time. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case, 5.5 Ah CAS rechargeable battery and charger.

Technical specifications

Temperature	50 – 500 °C	Function, hanger	Yes
Airflow rate	300 l/min	Function, life expectancy, motor	500 h
Temperature setting	in 10°C steps by joystick	Function, life expectancy, heating element	300 h
Settings made via	joystick	Replaceable heating element	No
Temperature display	LCD display	Restart protection	No
Airflow control	Settings	Temperature scanner	No
Programming function	Yes	Power supply, detail	Rechargeable lithium-ion battery
Loc function	No	Fine dust filter	No
Residual heat indicator	No	Thermal cut-out	Yes
Cool function	No	Thermostat	No
Motor, type	Brush motor	ESD	No
Heating element	Ceramic heating element	Nozzle receiver, type	34
Mains power supply	18 V	Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V	PU1, net weight	0,66 kg
Rechargeable battery capacity	5.5	Manufacturer's Warranty	1 year
Interface	Metabo rechargeable battery	PU1, EAN	4007841068356

Cordless hot air tool - Professional Line

mobile heat MH5

UK including rechargeable 5.5Ah battery and charger

EAN 4007841 068356

Article number 068356



Accessories

EAN 4007841 068257	Spare CAS battery 18V LiHD
EAN 4007841 068240	Spare CAS battery 18V LiHD
EAN 4007841 068349	CAS Fast Charger ASC 145
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 075811	Shrink tubing kit