

mobile heat MH3

including rechargeable 5.5Ah battery and charger

EAN 4007841 068226

Article number 068226



CE

Function description

Mobile heat MH3, the 18 V cordless hot air tool with 2 temperature settings (300°C/500°C). Heats up to 300°C in a maximum of 5 seconds. High-performance, with an airflow rate of up to 200 l/min. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case, with 5,5 Ah CAS rechargeable battery and charger.

Technical specifications

Temperature	300 – 500 °C	Function, hanger	Yes
Airflow rate	200 l/min	Function, life expectancy, motor	500 h
Temperature setting	2-stage	Function, life expectancy, heating element	300 h
Settings made via	multiple-stage switch	Replaceable heating element	No
Temperature display	LED segment display	Restart protection	No
Airflow control	Settings	Temperature scanner	No
Programming function	No	Power supply, detail	Rechargeable lithium-ion battery
Loc function	No	Fine dust filter	No
Residual heat indicator	No	Thermal cut-out	Yes
Cool function	No	Thermostat	No
Motor, type	Brush motor	ESD	No
Heating element	Ceramic heating element	Nozzle receiver, type	34
Mains power supply	18 V	Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V	PU1, net weight	2,2 kg
Rechargeable battery capacity	5.5	Manufacturer's Warranty	1 year
Interface	Metabo rechargeable battery	PU1, EAN	4007841068226

Cordless hot air tool - Professional Line

mobile heat MH3

including rechargeable 5.5Ah battery and charger

EAN 4007841 068226

Article number 068226



Accessories

EAN 4007841 068257	Spare CAS battery 18V LiHD
EAN 4007841 068240	Spare CAS battery 18V LiHD
EAN 4007841 068349	CAS Fast Charger ASC 145
EAN 4007841 068035	Adapter nozzle
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 058821	Pro Cut cutting system
EAN 4007841 006785	Pressure roller 40mm - Silicone