

Product data sheet

POCKET INFRARED THERMOMETER

A quick and easy infrared thermometer providing safe temperature measurement where non-contact access is required. Supplied complete with wrist strap.

Product features:

- Large LCD
- Temperature readings in °Celsius or °Fahrenheit
- Low battery indicator
- Wrist strap

Product specifications:

Temperature range:	-50 to 260°C (-58 to 500°F) (switchable)
Accuracy:	+/- 2% or +/- 2°C/°F
Resolution	0.1°C
Distance to spot ratio:	2:1
Response time:	0.5 seconds
Recommended measurement distance:	20 to 130mm
Emissivity:	0.95 fixed
Battery:	2 x AAA batteries (included)
Storage temperature:	-20 to 50°C (-4 to 122°F)
Working environment:	0 to 50°C / 10 to 95%RH (non-condensing)
CE/RoHS/WEEE:	Compliant
Hazard information (SDS):	See brannan.co.uk for information
LCD dimensions:	19 x 27mm
Product dimensions:	Net: 92.5 x 45 x 29.5mm Gross: 115 x 68mm x 30mm
Component weight:	Net: 65g Display box & instructions: 18g Gross: 83g



Description	Barcode	Product No
Pocket Infrared Thermometer	5 011405 387196	38/719/0

