

# Tab M10 Plus (3rd Gen) ZAAJ0385GB

## PSREF

Product Specifications  
Reference

### PERFORMANCE

#### Processor

MediaTek Helio G80 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

#### Graphics

Integrated ARM Mali-G52 MC2 GPU

#### Chipset

MediaTek SoC Platform

#### Memory

4GB Soldered LPDDR4x

#### Storage

128GB (eMCP, eMMC 5.1)

#### Expandable Memory

MicroSD Card (up to 1TB)

#### Card Reader

MicroSD Card Slot

#### Storage Support

- 128GB eMCP on systemboard (eMMC 5.1)
- MicroSD card, supports up to 1TB

#### Camera

Front 8.0MP (RGB) / Rear 8.0MP (RGB)

#### Microphone

Mono

#### Speakers

4 stereo speakers, 1W x4, optimized with Dolby® Atmos®

#### Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor

#### Vibration Motor

No support

#### Battery

Integrated 7500mAh (Min.) / 7700mAh (Typ.)

#### Max Battery Life

Standby time: 4 wks

Online video playback time: 12 hr

Web browsing time: 14 hr

Music playback time: 60 hr

#### Charging Time

Around 5 hr to fully charged

#### Power Adapter

5V / 2A

### DESIGN

#### Display

10.61" 2K (2000x1200) IPS 400nits Anti-fingerprint, 72% NTSC, Touch

#### Touchscreen

10-point Multi-touch

#### Case Material

PC + ABS, Metal

#### Pen

Pen Upgradable

#### Dimensions (WxDxH)

251.2 x 158.8 x 7.45 mm (9.89 x 6.25 x 0.29 inches)

#### Weight

Around 465 g (1.03 lbs)

#### Case Color

Storm Grey

### SOFTWARE

#### Operating System

Android™ 12 or later

### CONNECTIVITY

#### WLAN + Bluetooth®

11a/b/g/n/ac, 1x1 + BT5.0

#### WWAN

None

#### SIM Card

None

#### VoiceCall

No

#### Standard Ports

- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)

#### Optional Ports (configured)

1x microSD card slot (WLAN models)

### SERVICE

#### Base Warranty

1-year, Courier with 1-year Battery

### ACCESSORIES

#### Bundled Accessories

None

### CERTIFICATIONS

#### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

#### Other Certifications

TÜV Rheinland® Low Blue Light (Hardware Solution)

### MODEL

Product : TB125FU

TopSeller : No

Announce Date : 2022-03-16

EAN / UPC / JAN : 196800242853



- Lenovo reserves the right to change specifications or other product information without notice.
- Product image on this page is a sample, it may not match the real color of this model
- Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

## Premium Care - Advanced Support from Real People. Real Fast.

### REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.

### HASSLE FREE

‘Getting started’ and ‘how-to’ assistance for hardware and software. Easy solutions that are simple to reach – that’s how Premium Care delivers you the ideal support experience.

### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can’t be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

### Lenovo Active Pen 3 (2023)

ZG38C04479

With 4,096 levels of pressure and tilt detection, the Lenovo Active Pen 3 (2023) affords users the highest level of precision and control as they sketch or just take notes.

### Lenovo Precision Pen 2(US)

ZG38C03380

With 4,096 levels of pressure and tilt detection, the Lenovo Precision Pen 2 affords users the highest level of precision and control as they sketch or just take notes. With up to 100 hours usage\*, write or draw all d...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

## PSREF

Product Specifications  
Reference