

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200895003](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Tees and Splitters
Series	120089
IP Rating	IP67
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Taxonomy	Industrial Tees and Splitters
Type	Splitter - Solid Body
UPC	883906319472

Physical

Drop Connector	Nano-Change (M8)
Drop Gender	Male
Keyway	None
Left Trunk Connector	Nano-Change (M8)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	1.000/g
Poles	3
Right Trunk Connector	Nano-Change (M8)
Right Trunk Gender	Female
Temperature Range - Operating	-20°C to +90°C

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Material Info

Engineering Number	0808 04LMF 00001
--------------------	------------------

Reference - Drawing Numbers

Sales Drawing	SD-120089-002-001
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120089 Series](#)