



TECHNICAL INFORMATION

Watts:	40
Lumens:	4200
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	25,000 Hours
Unit Color:	PKW
Body Type:	Aluminium
Cutting Size:	207mm
PF:	>0.9
LED Chip Type:	COB
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	6500K
Dimension:	221x107mm

120 LUMEN REFLECTOR DOWNLIGHT | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 211280 - 40 PKW

[View more details](#)



FEATURES

- Downlight Series built with high quality COB LED chip
- Die cast aluminium housing with heat sink for optimum thermal management
- Multi-faceted aluminium reflector for focused light intensity
- Powerful LED light source with lumen efficiency of 120 LM/W
- No UV Radiation
- Suitable for residential, showrooms, hotels and boutiques etc.



PACKAGING

Gross Weight (Kgs): 1.25
Unit CBM: 0.009208
Dimension: 221x107mm

MASTER BOX PACKAGING

Box Qty: 12

LISTING DETAILS

Commodity Code: 8539520000
Ean Code: 3800157682541