



TECHNICAL INFORMATION

Watts:	5
Lumens:	540
Input Power:	AC:220-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Plastic+Metal
LED Chip Type:	SMD
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	3000K
Dimension:	71x93x100mm



FEATURES

- Perfect choice of Interior lighting for fabulous aesthetics and appeal
- Efficient LED driver and intruded heat sink for longer lifespan
- Robust Plastic+Metal build for efficient heat dissipation
- Suitable for decor, restaurants, residential, facades etc.

SINGLE HEAD | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218250 - 5 White

[View more details](#)

SINGLE HEAD WALL LAMP



Uses premium quality LEDs for a reliable, long-lasting, and energy saving light.

Modern minimalist directional lighting for residential and commercial areas.



PACKAGING

Gross Weight (Kgs):	0.41
Unit CBM:	0.001555
Dimension:	71x93x100mm

MASTER BOX PACKAGING

Box Qty:	24
Length (Box) mm:	110
Width (Box) mm:	105
Height (Box) mm:	110

LISTING DETAILS

Commodity Code:	9405114090
Ean Code:	3800157686464