



TECHNICAL INFORMATION

Watts:	12
Lumens:	1150
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	Grey
Body Type:	PC
LED Chip Type:	SMD
CRI:	>80
Beam Angle:	90°
Color Temperature:	4000K
Dimension:	230x100x90mm

SOFT LIGHTS LARGE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218243 - 12 Grey

[View more details](#)



SMD LED'S

Uses premium quality LEDs for a reliable, long-lasting, and energy saving light



FEATURES

- Modern range of Up-Down lights with sleek and stylish designs
- Elegant replacement for traditional up-down lighting
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Robust PC build for efficient heat dissipation
- Suitable for living rooms, pathways, balconies, facades etc.

PACKAGING

Gross Weight (Kgs):	0.73
Unit CBM:	0.00306
Dimension:	230x100x90mm

MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	240
Width (Box) mm:	100
Height (Box) mm:	110

LISTING DETAILS

Commodity Code:	9405423990
Ean Code:	3800157678759