



TECHNICAL INFORMATION

Watts:	4
Lumens:	476
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	Grey
Body Type:	Aluminium
LED Chip Type:	SMD
CRI:	>80
Dimmable:	No
Beam Angle:	15°/120°
Color Temperature:	4000K
Dimension:	200x90x90mm



FEATURES

- Modern range of Up-Down lights with sleek and stylish designs
- Elegant replacement for traditional up-down lighting
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Robust Aluminium build for efficient heat dissipation
- Suitable for living rooms, pathways, balconies, facades etc.

TRIANGLE LIGHT | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218300 - 4 Grey

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.97
Unit CBM: 0.00358
Dimension: 200x90x90mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 115
Width (Box) mm: 115
Height (Box) mm: 230

LISTING DETAILS

Commodity Code: 94051190
Ean Code: 3800157681285