



TECHNICAL INFORMATION

| | |
|------------------------|----------------------|
| Watts: | 200 |
| Lumens: | 19500 |
| Input Power: | AC:220-240V, 50/60Hz |
| Long Life: | 30,000 Hours |
| Unit Color: | Black |
| Body Type: | Aluminium |
| PF: | >0.9 |
| LED Chip Type: | SMD-Samsung Chip |
| CRI: | >80 |
| Operation Temperature: | -20°C to +40°C |
| Dimmable: | No |
| Beam Angle: | 110° |
| Color Temperature: | 4000K |
| Dimension: | 1059x130x96mm |



FEATURES

- Powerful LED light source with lumen efficiency of LM/W
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Excellent glare index for low mounting operations
- Longevity and efficient lumen maintenance
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums



PRO LINEAR LOWBAYS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21895 - 200 Black

[View more details](#)

SMD LED'S

PROVIDED BY SAMSUNG

Samsung chip for strong & efficient performance.
Heat and shock resistant.



PACKAGING

| | |
|---------------------|---------------|
| Gross Weight (Kgs): | 4.7 |
| Unit CBM: | 0.018464 |
| Dimension: | 1059x130x96mm |

MASTER BOX PACKAGING

| | |
|------------------|------|
| Box Qty: | 6 |
| Length (Box) mm: | 100 |
| Width (Box) mm: | 1110 |
| Height (Box) mm: | 135 |

LISTING DETAILS

| | |
|-----------------|---------------|
| Commodity Code: | 94054110 |
| Ean Code: | 3800157680837 |