



TECHNICAL INFORMATION

Watts:	150
Lumens:	14500
Input Power:	AC:220-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	798x130x96mm

PRO LINEAR LOWBAYS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21893 - 150 Black

[View more details](#)

SMD LED'S PROVIDED BY SAMSUNG

Samsung chip for strong & efficient performance.
Heat and shock resistant.



FEATURES

- Powerful LED light source with lumen efficiency of LM/W
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Excellent glare index for low mounting operations
- Longevity and efficient lumen maintenance
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums



PACKAGING

Gross Weight (Kgs): 3.85
Unit CBM: 0.014652
Dimension: 798x130x96mm

MASTER BOX PACKAGING

Box Qty: 6
Length (Box) mm: 105
Width (Box) mm: 850
Height (Box) mm: 135

LISTING DETAILS

Commodity Code: 94054210
Ean Code: 3800157680820