



#### TECHNICAL INFORMATION

Watts:	15
Lumens:	1620
Input Power:	AC:220-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Plastic+Metal
LED Chip Type:	SMD
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	4000K
Dimension:	605x100x115mm



#### FEATURES

- Perfect choice of Interior lighting for fabulous aesthetics and appeal
- Efficient LED driver and intruded heat sink for longer lifespan
- Robust Plastic+Metal build for efficient heat dissipation
- Suitable for decor, restaurants, residential, facades etc.

#### TRIPPLE HEAD | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 218261 - 15 Black

[View more details](#)

#### TRIPPLE HEAD WALL LAMP



Uses premium quality LEDs for a reliable, long-lasting, and energy saving light.

Modern minimalist directional lighting for residential and commercial areas.

**100°**  
Beam Angle

#### PACKAGING

Gross Weight (Kgs): 1.08  
Unit CBM: 0.00924  
Dimension: 605x100x115mm

#### MASTER BOX PACKAGING

Box Qty: 12  
Length (Box) mm: 610  
Width (Box) mm: 110  
Height (Box) mm: 120

#### LISTING DETAILS

Commodity Code: 9405114090  
Ean Code: 3800157686570