



#### TECHNICAL INFORMATION

Watts:	12
Lumens:	1250
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	Grey
Body Type:	PC
LED Chip Type:	SMD
CRI:	>80
Beam Angle:	170°
Color Temperature:	3000K
Dimension:	160x108x130mm
lumens per watt:	105



#### FEATURES

- Splendid designs made of high endurance PC material
- Ingress protection: (ip\_rating)
- Excellent heat dissipation
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Perfect lighting option for landscapes, gardens, patios etc.

#### OUTDOOR SQUARE LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 218337 - 12 Grey

[View more details](#)

#### SPECIAL FEATURES



Body Type: PC

Beam Angle : 170°

Sensor Compatible : Yes



#### PACKAGING

Gross Weight (Kgs):	0.5
Unit CBM:	0.00314
Dimension:	160x108x130mm

#### MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	140
Width (Box) mm:	115
Height (Box) mm:	170

#### LISTING DETAILS

Commodity Code:	9405423990
Ean Code:	3800157678995