



## TECHNICAL INFORMATION

Watts:	12
Lumens:	1200
Shape:	Square
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	PC
LED Chip Type:	SMD
CRI:	>80
Beam Angle:	150°
Color Temperature:	3000K
Dimension:	160x160x100mm
lumens per watt:	100



## FEATURES

- Splendid designs made of high endurance PC material
- Ingress protection: (ip\_rating)
- Excellent heat dissipation
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Perfect lighting option for landscapes, gardens, patios etc.

## OUTDOOR LIGHTS WITHOUT CAP | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 218543 - 12 Black

[View more details](#)



**SPECIAL  
FEATURES**

- Body Type: PC
- Color of Fixture : Black
- Sensor Compatible : Yes
- 150° Beam Angle



## PACKAGING

Gross Weight (Kgs):	0.61
Unit CBM:	0.00366
Dimension:	160x160x100mm

## MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	175
Width (Box) mm:	105
Height (Box) mm:	175

## LISTING DETAILS

Commodity Code:	9405423990
Ean Code:	3800157684972