



TECHNICAL INFORMATION

Watts:	12
Lumens:	1155
Shape:	Round
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	PC
LED Chip Type:	SMD
CRI:	>80
Beam Angle:	120°
Color Temperature:	3000K
Dimension:	169x100mm



FEATURES

- Splendid designs made of high endurance PC material
- Ingress protection: (ip_rating)
- Excellent heat dissipation
- Fitted with high quality SMD chips for better reliability and longer lifespan
- Perfect lighting option for landscapes, gardens, patios etc.

OUTDOOR LIGHTS CAP | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218537 - 12 Black

[View more details](#)

SPECIAL FEATURES



- Body Type: PC
- Color of Fixture : Black
- 120° Beam Angle
- Sensor Compatible : Yes

PACKAGING

Gross Weight (Kgs): 0.63
Unit CBM: 0.00366
Dimension: 169x100mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 175
Width (Box) mm: 105
Height (Box) mm: 175

LISTING DETAILS

Commodity Code: 9405423990
Ean Code: 3800157678988