



TECHNICAL INFORMATION

Watts:	12
Lumens:	1480
Shape:	Round
Input Power:	AC:200-240V,50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	270x65mm
lumens per watt:	120

SLIM DOME | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21820 - 12 White

[View more details](#)



FEATURES

- Fitted with high efficiency Samsung LED Chips
- Efficient thermal management technology
- 100% PC for endurance & durability
- IP65 rated protection
- Suitable for open areas constantly exposed to dust and moisture like parking_x000D_ lots, corridors, airports, and malls

PACKAGING

Gross Weight (Kgs):	0.76
Unit CBM:	0.000873
Dimension:	270x65mm

MASTER BOX PACKAGING

Box Qty:	10
Length (Box) mm:	280
Width (Box) mm:	75
Height (Box) mm:	280

LISTING DETAILS

Commodity Code:	94051140
Ean Code:	3800157687508