



TECHNICAL INFORMATION

Watts:	5
Lumens:	800
Input Power:	AC:220-240V,50Hz
Long Life:	20,000 Hours
Unit Color:	Grey
Body Type:	Aluminium
LED Chip Type:	SMD
CRI:	>80
Dimmable:	No
Beam Angle:	350°
Color Temperature:	4000K
Dimension:	115x50x100mm



FEATURES

- Well-designed 360° rotatable wall light
- Fitted with high quality LEDs for better reliability
- Efficient LED driver and intruded heat sink for longer lifespan
- Suitable for decor, restaurants, residential, facades etc.

SINGLE HEAD ROTATABLE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218291 - 5 Grey

[View more details](#)



PACKAGING

Gross Weight (Kgs): 0.59
 Unit CBM: 0.00086
 Dimension: 115x50x100mm

MASTER BOX PACKAGING

Box Qty: 20
 Length (Box) mm: 120
 Width (Box) mm: 70
 Height (Box) mm: 100

LISTING DETAILS

Commodity Code: 94051190
 Ean Code: 3800157681414