



TECHNICAL INFORMATION

Watts:	6
Lumens:	490
Shape:	Square
Input Power:	AC:85-265V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Aluminium
Cutting Size:	110x100mm
PF:	>0.7
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	120°
Color Temperature:	6400K
Dimension:	120x120x12mm



FEATURES

- Strong and sturdy Aluminium body
- Designed with high efficiency LED SMD chips.
- Easy to connect driver
- Non Dimmable driver included
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.



PREMIUM SERIES SQUARE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 214865 - 6 White

[View more details](#)

SMD LED'S

Equipped with high quality LEDs with
No flickers & No UV Radiation

Instant Start-up
0-100% in less than 1s



PACKAGING

Gross Weight (Kgs): 0.21
Unit CBM: 0.000757
Dimension: 120x120x12mm

MASTER BOX PACKAGING

Box Qty: 40

LISTING DETAILS

Ean Code: 3800157686112